

Кондуктометры–термометры стационарные DELTA OHM HD 2206.2

Технические характеристики

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81
Киргизия (996)312-96-26-47

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Казахстан (772)734-952-31

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Таджикистан (992)427-82-92-69

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

Единый адрес для всех регионов: dmh@nt-rt.ru || www.deltaohm.nt-rt.ru

HD 2206.2



HD 2206.2 BENCH-TOP CONDUCTIVITY METER

The **HD2206.2** is a bench top instrument for electrochemical measures: **conductivity** and **temperature**. It is fitted with a large backlit LCD display.

The **HD2206.2** measures **conductivity**, **resistivity** in liquids, **total dissolved solids (TDS)**, and **salinity** with combined 4-ring and 2-ring conductivity/temperature probes. The conductivity probes can have a direct input or with SICRAM module. The inputs are separate.

The instrument is fitted with input for the measurement of **temperature** with Pt100 or Pt1000 immersion, penetration or contact probes. The temperature probes are equipped with an automatic recognition module and factory calibration data are stored inside.

- The conductivity probe calibration can be performed automatically with automatically detected conductivity calibration solutions: 147µS/cm, 1413µS/cm, 12880µS/cm or 111800µS/cm or manually with calibration solutions having different values.
- Conductivity and temperature probes fitted with SICRAM module can store factory and calibration data inside.

The instrument HD2206.2 is a **datalogger**, it can memorize up to 2,000 samples of data of conductivity (or resistivity or TDS or salinity) and temperature.

The data can be transferred from the instrument connected to a PC via the RS232C and USB 2.0 serial ports. The storing parameters can be configured using the menu.

The RS232C serial port can be used to transfer the acquired measurements to a 24 column portable printer in real time (HD40.1 or HD40.2). The instruments equipped with **HD22BT** (Bluetooth) option can transfer data without any connection to a PC or printer fitted with Bluetooth input or through Bluetooth/RS232C converter. The software DeltaLog11 allows instrument management and configuration, and data processing on PC.

The instruments have IP66 protection degree.

Technical characteristics HD2206.2

X - Ω - TDS - NaCl - °C - °F measurement

Instrument

Dimensions (Length x Width x Height)	265x185x70mm
Weight	490g
Materials	ABS, rubber
Display	Back lighted, matrix point display. 240x64 points, visible area: 128x35mm

Operating conditions

Working temperature	-5 ... 50°C
Storage temperature	-25 ... 65°C
Working relative humidity	0 ... 90% R.H. without condensate

Protection degree

IP66

Power

Auxiliary socket	Mains adapter (cod. SWD10) 12Vdc/1A For supplying of electrode holder with built-in stirrer HD22.2
------------------	---

Security of memorized data

Unlimited

Time

Date and hour	Real time schedule with backup battery 3.6V - ½AA
Accuracy	1min/month max drift

Measured values storing

Quantity	2000 screens
Storage interval	1s ... 999s

Calibration storage


Quantity	Last 8 calibrations of each physical quantity
----------	---

RS232C serial interface

Type	RS232C electrically isolated
Baud rate	Can be set from 1200 to 115200 baud
Data bit	8
Parity	None
Stop bit	1
Flow Control	Xon/Xoff
Length of serial cable	Max 15m

Data Interface

USB	1.1 - 2.0 electrically isolated
Bluetooth Interface	optional



Connections

Input for temperature probes with SICRAM module ⑤	8-pole male DIN45326 connector
2/4 ring direct conductivity input	8-pole male DIN45326 connector
Conductivity probe with SICRAM module input ⑦	8-pole male DIN45326 connector
Serial interface	DB9 connector (9- pole male)
USB interface	USB connector type B
Bluetooth	Optional
Mains adapter	2 -pole (Ø5.5mm-2.1mm). Positive at centre
Socket for power supply of electrode holder with built-in magnetic stirrer	2- pole connector (Ø5.5mm-2.1mm). Positive at centre (output 12Vdc/200mA max).

Measurement of conductivity by instrument

Measuring range (Kcell=0.01)	0.000...1.999µS/cm	Resolution	0.001µS/cm
Measuring range (Kcell=0.1)	0.00...19.99µS/cm		0.01µS/cm
Measuring range (K cell=1)	0.0...199.9µS/cm		0.1µS/cm
	200...1999µS/cm		1µS/cm
	2.00...19.99mS/cm		0.01mS/cm
	20.0...199.9mS/cm		0.1mS/cm
Measuring range (Kcell=10)	200...1999mS/cm		1mS/cm
Accuracy (conductivity)	±0.5% ±1digit		

Measurement of resistivity by instrument

Measuring range (Kcell=0.01)	Up to 1GΩ·cm	(*)
Measuring range (Kcell=0.1)	Up to 100MΩ·cm	(*)
Measuring range (K cell=1)	5.0...199.9Ω·cm	0.1Ω·cm
	200...999Ω·cm	1Ω·cm
	1.00k...19.99kΩ·cm	0.01kΩ·cm
	20.0k...99.9kΩ·cm	0.1kΩ·cm
	100k...999kΩ·cm	1kΩ·cm
	1...10MΩ·cm	1MΩ·cm
Measuring range (Kcell=10)	0.5...5.0Ω·cm	0.1Ω·cm
Accuracy (resistivity)	±0.5% ±1digit	

Measurement of total dissolved solids (with coefficient χ /TDS=0.5)

Measuring range (Kcell=0.01)	0.00...1.999mg/l	0.005mg/l
Measuring range (Kcell=0.1)	0.00...19.99mg/l	0.05mg/l
Measuring range (K cell=1)	0.0...199.9 mg/l	0.5 mg/l
	200...1999 mg/l	1 mg/l
	2.00...19.99 g/l	0.01 g/l
	20.0...199.9 g/l	0.1 g/l
Measurement range (Kcell=10)	100...999 g/l	1 g/l
Accuracy (total dissolved solids)	±0.5% ±1digit	

Measurement of salinity

Measuring range	0.000...1.999g/l	Resolution	1mg/l
	2.00...19.99g/l		10mg/l
	20.0...199.9 g/l		0.1 g/l
Accuracy (salinity)	±0.5% ±1digit		

Automatic/manual temperature compensation

0...100°C with $\alpha_T = 0.00...4.00\%/^{\circ}\text{C}$

Reference temperature

0...50°C

χ /TDS conversion factor

0.4...0.8

Cell constants K (cm^{-1}) already set

on the instrument

Cell constants K (cm^{-1}) that can be

set by user

0.01...20.00

Standard solutions automatically detected (@25°C)

147µS/cm
1413µS/cm
12880µS/cm
111800µS/cm

Measurement of temperature by instrument

Pt100 measuring range	-50...+150°C
Pt1000 measuring range	-50...+150°C
Resolution	0.1°C
Accuracy	±0.1°C ±1digit
Drift after 1 year	0.1°C/year

(*) The resistivity measurement is obtained from the reciprocal of conductivity measurement. Close to the bottom of the scale, the indication of resistivity appears like reported in the table below:

K cell = 0.01 cm^{-1}		K cell = 0.1 cm^{-1}	
Conductivity (µS/cm)	Resistivity (MΩ·cm)	Conductivity (µS/cm)	Resistivity (MΩ·cm)
0.001 µS/cm	1000 MΩ·cm	0.01 µS/cm	100 MΩ·cm
0.002 µS/cm	500 MΩ·cm	0.02 µS/cm	50 MΩ·cm
0.003 µS/cm	333 MΩ·cm	0.03 µS/cm	33 MΩ·cm
0.004 µS/cm	250 MΩ·cm	0.04 µS/cm	25 MΩ·cm

TECHNICAL DATA OF PROBES AND MODULES EQUIPPED WITH INSTRUMENT Temperature probes Pt100 sensor with SICRAM module

Model	Type	Application field	Accuracy
TP472I	Immersion	-196°C...+500°C	±0.25°C (-196°C...+300°C) ±0.5°C (+300°C...+500°C)
TP472I.0 1/3 DIN Thin Film	Immersion	-50°C...+300°C	±0.25°C (-50°C...+300°C)
TP473P.I	Penetration	-50°C...+400°C	±0.25°C (-50°C...+300°C) ±0.5°C (+300°C...+400°C)
TP473P.0 1/3 DIN Thin Film	Penetration	-50°C...+300°C	±0.25°C (-50°C...+300°C)
TP474C.I	Contact	-50°C...+400°C	±0.3°C (-50°C...+300°C) ±0.5°C (+300°C...+400°C)
TP474C.0 1/3 DIN Thin Film	Contact	-50°C...+300°C	±0.3°C (-50°C...+300°C)
TP475A.0 1/3 DIN Thin Film	Air	-50°C...+250°C	±0.3°C (-50°C...+250°C)
TP472I.5	Penetration	-50°C...+400°C	±0.3°C (-50°C...+300°C) ±0.6°C (+300°C...+400°C)
TP472I.10	Penetration	-50°C...+400°C	±0.30°C (-50°C...+300°C) ±0.6°C (+300°C...+400°C)
TP49A.0 Class A Thin Film	Immersion	-70°C...+250°C	±0.3°C (-70°C...-50°C) ±0.25°C (-50°C...+250°C)
TP49AC.0 Class A Thin Film	Contact	-70°C...+250°C	±0.3°C (-70°C...-50°C) ±0.25°C (-50°C...+250°C)
TP49AP.0 Class A Thin Film	Penetration	-70°C...+250°C	±0.3°C (-70°C...-50°C) ±0.25°C (-50°C...+250°C)
TP875.I	Globe-thermometer Ø150mm	-30°C...+120°C	±0.25°C
TP876.I	Globe-thermometer Ø50mm	-30°C...+120°C	±0.25°C
TP87.0 1/3 DIN Thin Film	Immersion	-50°C...+200°C	±0.25°C
TP878.0 1/3 DIN Thin Film	Photovoltaic	+4°C...+85°C	±0.25°C
TP878.1.0 1/3 DIN Thin Film			
TP879.0 1/3 DIN Thin Film	Compost	-20°C...+120°C	±0.25°C

Common characteristics

Temperature drift @ 20°C 0.003%/°C



4 wires Pt100 and 2 wires Pt1000 Probes

Model	Type	Application field	Accuracy
TP47.100.0 1/3 DIN Thin Film	4 wires Pt100	-50...+250°C	1/3 DIN
TP47.1000.0 1/3 DIN Thin Film	2 wires Pt1000	-50...+250°C	1/3 DIN
TP87.100.0 1/3 DIN Thin Film	4 wires Pt100	-50...+200°C	1/3 DIN
TP87.1000.0 1/3 DIN Thin Film	2 wires Pt1000	-50...+200°C	1/3 DIN

Common features

Temperature drift @20°C

Pt100 0.003%/°C

Pt1000 0.005%/°C

ORDERING CODES

HD2206.2: The kit is composed of: instrument HD2206.2 for the measurement of conductivity - resistivity - TDS - salinity - temperature, **data logger**, stabilized power supply at mains voltage 100-240Vac/12Vdc-1A., instructions manual and software DeltaLog11.

Conductivity probes, temperature probes, standard reference solutions, cables for data download to PC or printer have to be ordered separately.

ACCESSORIES

9CPRS232: Connection cable SubD female 9- pole for serial output RS232C.

CP22: USB 2.0 connection cable - connector type A - connector type B.

DeltaLog11: Software for download and management of the data on PC using Windows operating systems.

SWD10: Stabilized power supply at 100...240Vac/12Vdc-1A mains voltage.

HD40.1: 24-column portable thermal printer, **serial interface**, 57mm paper width, four NiMH 1.2V rechargeable batteries, SWD10 power supply, instruction manual, 5 thermal paper rolls. Requires the cable 9CPRS232 (**optional**).

HD40.2: 24-column portable thermal printer, **Bluetooth and serial interface**, 57mm paper width, four NiMH 1.2V rechargeable batteries, SWD10 power supply, instruction manual, 5 thermal paper rolls. Requires the module HD22BT (**optional**) or the cable 9CPRS232 (**optional**).

HD22.2: Laboratory electrode holder composed of basis plate with incorporated magnetic stirrer, staff and replaceable electrode holder. Height max. 380mm. Powered by bench-top meters of the series HD22... with cable HD22.2.1 (**optional**) or supplier SWD10 (**optional**).

HD22.3: Laboratory electrode holder with metal basis plate. Flexible electrode holder for free positioning. For Ø 12mm probes.

HD22BT: Bluetooth module for wireless data transmission from instrument to PC. **The fitting of the module into the instrument is made exclusively by Delta Ohm, at the time of placing the order.**

Conductivity probes and combined conductivity and temperature probes without SICRAM module (Input Ⓢ)

SPO6T: Combined conductivity and temperature 4-electrode cell in Platinum, body in Poca. Cell constant K = 0.7. Measurement range 5µS/cm ...200mS/cm, 0...90°C. Max. pressure 5bar.

SPT401.001: Combined conductivity and temperature 2- electrode cell in stainless steel AISI 316. Cell constant K = 0.01. Measurement range 0.04µS/cm ...20µS/cm, 0...120°C. Measurement in closed-cell. Max.pressure 5bar.

SPT01G: Combined conductivity and temperature 2-electrode Platinum-wire cell, body in glass. Cell constant K = 0.1. Measurement range 0.1µS/cm ...500µS/cm, 0...80°C. Max.pressure 5bar.

SPT1G: Combined conductivity and temperature 2-electrode Platinum-wire cell, body in glass. Cell constant K = 1. Measurement range 10µS/cm ...10mS/cm, 0...80°C. Max. pressure 5bar.

SPT10G: Combined conductivity and temperature 2-electrode Platinum-wire cell, body in glass. Cell constant K = 10. Measurement range 500µS/cm ...200mS/cm, 0...80°C. Max.pressure 5bar.

Probe dimensions and characteristics at page WA-77

Combined conductivity / temperature probes with SICRAM module (Input Ⓢ)

SPT1GS: Combined conductivity /temperature 2-electrode Platinum- wire cell, body in glass with SICRAM module. Cell constant K = 1. Measuring range 10µS/cm ...10mS/cm, 0...80°C. Max.pressure 5bar.

Probe dimensions and characteristics at page WA-77

Standard conductivity calibration solutions

HD8747: Standard calibration solution 0.001mol/l equal to 147µS/cm @25°C - 200cc.

HD8714: Standard calibration solution 0.01mol/l equal to 1413µS/cm @25°C - 200cc.

HD8712: Standard calibration solution 0.1mol/l equal to 12880µS/cm @25°C - 200cc.

HD87111: Standard calibration solution 1mol/l equal to 111800µS/cm @25°C - 200cc.

Temperature probes complete with SICRAM module

TP472I: Wire wound Pt100 sensor, immersion probe. Stem Ø 3 mm, length 300 mm. Cable length 2 m.

TP472I.0: Thin film Pt100 sensor, immersion probe. Stem Ø 3 mm, length 230 mm. Cable length 2 m.

TP473P: Wire wound Pt100 sensor, penetration probe. Stem Ø 4mm, length 150 mm. Cable length 2 m.

TP473P.0: Thin film Pt100 sensor, penetration probe. Stem Ø 4mm, length 150 mm. Cable length 2 m.

TP474C: Wire wound Pt100 sensor, contact probe. Stem Ø 4mm, length 230mm, contact surface Ø 5mm. Cable length 2 m.

TP474C.0: Thin film Pt100 sensor, contact probe. Stem Ø 4mm, length 230mm, contact surface Ø 5mm. Cable length 2 m.

TP475A.0: Thin film Pt100 sensor, air probe. Stem Ø 4mm, length 230mm. Cable length 2 m.

TP472I.5: Thin film Pt100 sensor, penetration probe. Stem Ø 6mm, length 500 mm. Cable length 2 m.

TP472I.10: Thin film Pt100 sensor, penetration probe. Stem Ø 6mm, length 1000mm. Cable length 2 m.

TP49A.0: Thin film Pt100 sensor, immersion probe. Stem Ø 2,7mm, length 150mm. Cable length 2 m. Aluminium handle

TP49AC.0: Thin film Pt100 sensor, contact probe. Stem Ø 4mm, length 150mm. Cable length 2 m. Aluminium handle

TP49AP.0: Thin film Pt100 sensor, penetration probe. Stem Ø 2,7mm, length 150mm. Cable length 2 m. Aluminium handle

TP875.I: Wire wound Pt100 sensor, 150mm diameter globe-thermometer equipped with handle. Cable length 2 m.

TP876.I: Wire wound Pt100 sensor, 50mm diameter globe-thermometer equipped with handle. Cable length 2 m.

TP87.0: Thin film Pt100 sensor, immersion probe. Stem Ø 3 mm, length 70 mm. Cable length 2 m.

TP878.0: Thin film Pt100 sensor, contact probe for solar panels. Cable length 2 m.

TP878.1.0: Thin film Pt100 sensor, contact probe for solar panels. Cable length 5 m.

TP879.0: Thin film Pt100 sensor, penetration probe for compost. Stem Ø 8 mm, length 1000 mm. Cable length 2 m.

Temperature probes without SICRAM module

TP471.00.0: Thin film Pt100 sensor, immersion probe. Stem Ø 3mm, length 230mm. Connection cable 4 wires with connector, length 2 m.

TP47.1000.0: Thin film Pt1000 sensor, immersion probe. Probe's Stem Ø 3mm, length 230mm. Connection cable 4 wires with connector, length 2 m.

TP47: Connector for Pt100 4-wire and Pt1000 2-wire probes without SICRAM module.

TP87.100.0: Thin film Pt100 sensor, immersion probe. Stem Ø 3mm, length 70mm. 4-wires connection cable with connector, length 1 m.

TP87.1000.0: Thin film Pt1000 sensor, immersion probe. Stem Ø 3mm, length 70mm. 2-wires connection cable with connector, length 1 m.



HD40.1

HD22.3

Архангельск (8182)63-90-72	Ижевск (3412)26-03-58	Магнитогорск (3519)55-03-13	Пермь (342)205-81-47	Сургут (3462)77-98-35
Астана (7172)727-132	Иркутск (395)279-98-46	Москва (495)268-04-70	Ростов-на-Дону (863)308-18-15	Тверь (4822)63-31-35
Астрахань (8512)99-46-04	Казань (843)206-01-48	Мурманск (8152)59-64-93	Рязань (4912)46-61-64	Томск (3822)98-41-53
Барнаул (3852)73-04-60	Калининград (4012)72-03-81	Набережные Челны (8552)20-53-41	Самара (846)206-03-16	Тула (4872)74-02-29
Белгород (4722)40-23-64	Калуга (4842)92-23-67	Нижний Новгород (831)429-08-12	Санкт-Петербург (812)309-46-40	Тюмень (3452)66-21-18
Брянск (4832)59-03-52	Кемерово (3842)65-04-62	Новокузнецк (3843)20-46-81	Саратов (845)249-38-78	Ульяновск (8422)24-23-59
Владивосток (423)249-28-31	Киров (8332)68-02-04	Новосибирск (383)227-86-73	Севастополь (8692)22-31-93	Уфа (347)229-48-12
Волгоград (844)278-03-48	Краснодар (861)203-40-90	Омск (3812)21-46-40	Симферополь (3652)67-13-56	Хабаровск (4212)92-98-04
Вологда (8172)26-41-59	Красноярск (391)204-63-61	Орел (4862)44-53-42	Смоленск (4812)29-41-54	Челябинск (351)202-03-61
Воронеж (473)204-51-73	Курск (4712)77-13-04	Оренбург (3532)37-68-04	Сочи (862)225-72-31	Череповец (8202)49-02-64
Екатеринбург (343)384-55-89	Липецк (4742)52-20-81	Пенза (8412)22-31-16	Ставрополь (8652)20-65-13	Ярославль (4852)69-52-93
Иваново (4932)77-34-06	Киргизия (996)312-96-26-47	Казахстан (772)734-952-31	Таджикистан (992)427-82-92-69	

Единый адрес для всех регионов: dmh@nt-rt.ru || www.deltaohm.nt-rt.ru